

## Standard heating mantles series WMO-GF

for operating temperatures up 450°C



- for reaction vessels flat flange with volume up to 10l
- for operating temperatures up to 450°C
- flexible glass yarn heating element  
*an even heat transfer and a gentle treatment  
of the glassware*
- high quality design  
*made by hand work*
- thermally insulated and earthed
- sizes from 500 ml with Ø 60 mm bottom hole
- four standard mounting clips  
*with appropriate accessories a minimum of effort  
allows to ensure a tilt-proof set-up or to integrate  
within support wall*
- with residual current detection (RCD)
- **CE**

*our heating mantles perform the requirements based  
on the European harmonised standards*



## Technical specification

## WMO-GF

Nominal voltage	230 V AC
Nominal power output	see ordering details
Heating zones	see ordering details
Safety class	I
System of protection	IP 00
Heating element temperature	max. 450°C
Power supply cable	1,5 m with schuko-plug (earthed), heating zone switch and RCD switch

## Heating-zone selection

Switch position	0	1	2	3	4
2 heating zones					
Power	0	1/4	1/2	1/1	
4 heating zones					
Power	0	1/4	1/2	3/4	1/1

## Ordering details

Volume ml / l	Vessel Ø x H mm	Power W	Heating zones	Part.-No.
100	70 x 85	100	2	96300100
250	70 x 125	200	2	96300250
500	106 x 120	250	2	96300500
1	106 x 205	500	2	96301000
2	140 x 270	800	2	96302000
4	200 x 290	1400	4	96304000
6	215 x 320	1600	4	96306000
10	240 x 410	2400	4	96310000

We also manufacture special heating mantles with other specifications – available on request

## Accessories

We supply a full range of controllers and temperature controllers.

**MOHR & CO**  
Laborhandels-gesellschaft mbH

D-69181 Leimen  
Gottlieb-Daimler-Straße 2

Phone + 49 (0) 6224 7 10 93 + 94  
Fax + 49 (0) 6224 7 70 12

info@labo-mohr.de  
www.labo-mohr.de