

## Serial heating unit series HM-R3

for operating temperatures up to 450°C



- bank unit with three heating positions for flasks, round bottom
- flexible glass yarn heating element  
*an even heat transfer and a gentle treatment of the glassware*
- each heating position with built-in controller  
*allows a continuous adjustment of power outlet*
- plastic-coated metal housing  
*characterised by a chemical-resistant metal housing providing excellent stability*
- thermally insulated and earthed
- predrilled threaded hole on rear allows to fix the clamp HM-SK (accessories) for each position
- with residual current detection (RCD)



*our heating mantles perform the requirements based on the European harmonized standards*



## Technical specification

## HM-R3

Nominal voltage	230 V AC
Nominal power output	see ordering details
Heating zones	see ordering details
Safety class	I
System of protection	casing IP 43, heating surface IP 00
Heating element temperature	max. 450°C
Power supply cable	1,5 m with schuko-plug (earthed) and RCD switch

## Ordering details

Volume ml	Flask Ø mm	Power W	Heating zone	Dimensions B x H x T mm	Part.-No.
3 x 100	3 x 64	3 x 110	1	580 x 150 x 290	93300100
3 x 250	3 x 85	3 x 220	1	580 x 150 x 290	93300250
3 x 500	3 x 105	3 x 330	1	580 x 150 x 290	93300500
3 x 1000	3 x 131	3 x 495	1	580 x 150 x 290	93301000

## Accessories

Support clamp type HM-SK	Part.-No. 97000001
to fix support rods with diameter up to Ø 13 mm each position	

# MOHR & CO

Winkler AG  
D-69181 Leimen

Gottlieb-Daimler-Straße 2  
Tel. + 49 (0) 6224 7 10 93 + 94

mohr@labo-mohr.de  
www.labo-mohr.de